



EN ISO 20345:2011



CRYSTAL  
**BIELLA**  
**86205-00**

**S2 \*CI SRC**

**Size:** 35-39 40-48

**Weight:** 490 gr.

**Fit:** 11

**Working Environment:**  
Food and Chemical industry,  
Ho.Re.Ca.



## FEATURES

### UPPER

MicroFiber XPRO 1,8-2,0 mm

### LINING

Bacteriostatic Teklife 3D

### ANTISLIP LINING

DUALMICRO

### INSOLE

Flyfit

### TOE CAP

Fiber cap SXT

### TYPE

Low Shoe

### SOLE

**PU DUAL-DENSITY SRC**

Double density PU outsole with tread designed mainly for indoor use. Self-cleaning design and highly non-slip grip. SRC Antislip standard.

## TECHNOLOGIES

### Removable Insole



**FLYFIT**

The upper layer in contact with the foot is made of a highly resistant netting to ensure exceptional absorption of dampness. A self-forming antibacterial foam layer ensures comfort and correct support of the foot.



### Protection elements

**fibercap sxt**

Composite toecap, reinforced with fiberglass. Structure with a variable thickness for better performances



## SRC (SRA+SRB)



SOLE 86  
PU - PU

<b>SRA</b> CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32 HEEL (CONTACT ANGLE °) ≥0.28	<b>0.40</b> <b>0.32</b>
<b>SRB</b> STEEL + GLYCEROL	FLAT ≥0.18 HEEL (CONTACT ANGLE °) ≥0.13	<b>0.19</b> <b>0.24</b>

EN ISO 20344:2011

### Lateral stability

**dynamic HC control**  
technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



### Torsional stability

**STABIL•ACTIVE**

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



### Electrical features



Wire Electricity Discharge

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



### Other

**DUALMICRO**  
**DUALMICRO**

Double non-slip layer of microfibre, resistant up to 200,000 cycles. Makes the footwear more comfortable, blocking the foot during use.