



EN ISO 20347:2012


 HORIZON
CUPRA
 53071-24

01 FO SRC
Size: 36-48
Weight: 495 gr.

Fit: 10,5

Working Environment:
 Multipurpose, Logistics and Light Industry


FEATURES

UPPER

Drummed Suede Leather 1,8-2,0 mm

LINING

3D Air circulation 320 gr.

ANTISLIP LINING
 DUALMICRO

INSOLE

Flyfit

TYPE

Low Shoe



SOLE

PU DUAL-DENSITY SRC

Two-component PU sole with self-cleaning pattern, extremely flexible for various places of use, both indoor and outdoor, with SRC Antislip Standard.



SRC (SRA+SRB)

		SOLE 52 - 53 PU - PU
SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32 HEEL (CONTACT ANGLE °) ≥0.28	0.36 0.42
SRB STEEL + GLYCEROL	FLAT ≥0.18 HEEL (CONTACT ANGLE °) ≥0.13	0.19 0.14

EN ISO 20344:2011

TECHNOLOGIES

Removable Insole


FLYFIT

The upper layer in contact with the foot is made of a highly resistant netting to ensure exceptional absorption of dampness. A self-forming antibacterial foam layer ensures comfort and correct support of the foot.



Protection elements


EN ISO 20347:2012

"Occupational" footwear with all the physico-chemical characteristics and the comfort of Sixton footwear. Footwear without safety toecap, with no anti-perforation insert.

Lateral stability

dynamic HC control
 technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability


STABIL • ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features



Wire Electricity Discharge

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



Other

DUALMICRO
DUALMICRO

Double non-slip layer of microfibre, resistant up to 200,000 cycles. Makes the footwear more comfortable, blocking the foot during use.