



EN ISO 20345:2022


 SKIPPER
ADRIA HIGH
94391-03
S2 FO *CI SR
Size: 38-48
Weight: 510 gr.

Fit: 11

Working Environment:
 Food and Chemical industry,
 Ho.Re.Ca., Multipurpose, ESD
 Areas


FEATURES

UPPER

MicroFiber XPRO 1,8-2,0 mm

LINING

Bacteriostatic Teklife 3D

ANTISLIP LINING

DUALMICRO

INSOLE

Five 4 Fit

TOE CAP

Alu SXT 2.0 Toe cap

TYPE

Ankle boot

SOLE

PU / PU ESD-PLUS SRC

Double density PU sole, Outer- and in-between sole with ESD compound. For use in contact with sensitive electronic equipment. Light and comfortable, very versatile, highly non-slip SRC Antislip standard.

TECHNOLOGIES

Removable Insole

FIVE 4 FIT

Highly breathable and absorbent anatomic insole. Multilayer structure to take advantage of the peculiarities of each component. Dry and with a comfortable memory foam "pillow"



Protection elements

alu-sxt 2.0
 aluminium

The result of the evolution of the latest aluminium technologies. A new multi-thicknesses toe cap, which delivers a highly performing protection where needed. Ultralight protection, keeping comfortable inner volumest.



Lateral stability

dynamic HC control
 technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features




ESD footwear discharge static electricity and avoid damaging surrounding objects; they are designed in compliance with the following standards: IEC EN 61340-5-1:2016 - IEC EN 61340-4-3:2018 - IEC EN 61340-4-5:2018.

Other

SXT H.ABC
 HIGH ANTIBACTERIAL COMPONENT

Created for those who work in the HORECA sector, H.ABC footwear has new antibacterial components subjected to analysis by accredited laboratories. The results confirm the constant elimination activity of over 80% of bacterial load.



PU - PU

SOLE 94

SLIP RESISTANCE

EN ISO 20344:2021

BASIC

 CERAMIC WITH
 NALS

FORWARD HEEL SLIP ≥ 0.31	0,34
BACKWARD FOREPART SLIP ≥ 0.36	0,40



SR

 CERAMIC WITH
 GLYCERINE

FORWARD HEEL SLIP ≥ 0.19	0,29
BACKWARD FOREPART SLIP ≥ 0.22	0,40

