



EN ISO 20347:2022



SKIPPER LADY

CIMA
96398-05
OB A E FO SR
Size: 35-42 Lady

Weight: 360 gr.

Fit: 11

Working Environment:

Multipurpose, Components and Automotive



FEATURES

UPPER

Digitex Hydro Airy
 MicroFiber Suede 1,6-1,8 mm
 Digitex Hydro Airy
 MicroFiber Suede with Pro-tech
 SXT light 1,6-1,8 mm

LINING

Breezy 3D, two-layers
 combination

ANTISLIP LINING

DUALMICRO

INSOLE

Five 4 Fit

TOE CAP

TYPE

Low Shoe

SOLE

PU DUAL-DENSITY SRC

Double density PU outsole with
 tread designed mainly for indoor
 use. Self-cleaning design and
 highly non-slip grip.

TECHNOLOGIES

Removable Insole

FIVE 4 FIT

Highly breathable and absorbent
 anatomic insole. Multilayer structure
 to take advantage of the peculiarities
 of each component. Dry and with a
 comfortable memory foam "pillow"



Protection elements



EN ISO 20347:2012

Puncture resistant recycled non-
 metallic insert plus 1100N.

Lateral stability

dynamic HC control
 technology

Ergonomic rigid internal structure. It
 houses the heel into the right seat,
 adjusting the foot support and control
 of the ankle sideways movements. It
 keeps the foot tight to the shoe,
 allowing the perfect fit.



Torsional stability



Support made of rigid plastic
 material. It stabilizes the heel bone,
 the instep and tarsal joints, without
 altering energy absorption. A support
 for the natural movement of the foot;
 it provides comfort and greater
 stability.



Electrical features



ESD footwear discharge static
 electricity and avoid damaging
 surrounding objects; they are
 designed in compliance with the
 following standards: IEC EN
 61340-5-1:2016 - IEC EN
 61340-4-3:2018 - IEC EN
 61340-4-5:2018.

Other

DUALMICRO
DUALWICKO

Double non-slip layer of microfibre,
 resistant up to 200,000 cycles. Makes
 the footwear more comfortable,
 blocking the foot during use.



PU - PU

SOLE 95

SLIP RESISTANCE

EN ISO 20344:2021

BASIC

CERAMIC WITH
 NALS

FORWARD
 HEEL SLIP
 ≥ 0.31

0,32

BACKWARD
 FOREPART SLIP
 ≥ 0.36

0,39



SR

CERAMIC WITH
 GLYCERINE

FORWARD
 HEEL SLIP
 ≥ 0.19

0,26

BACKWARD
 FOREPART SLIP
 ≥ 0.22

0,30

