



EN ISO 20345:2022/A1:2024



SKIPPER LADY

CIMA

95398-02L

S3S FO *CI SR

Size: 35-42 Lady

Weight: 420 gr.

Fit: 11

Working Environment:

Logistics and Light Industry, Components and Automotive, ESD Areas



FEATURES

UPPER

Digitex Hydro Airy MicroFiber Suede with Pro-tech SXT light 1,6-1,8 mm

LINING

Breezy 3D, two-layers combination

ANTISLIP LINING

DUALMICRO

INSOLE

Five 4 Fit "lady"

TOE CAP

Alu SXT 2.0 Toe cap

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Low Shoe

SOLE

PU DUAL-DENSITY SRC

Double density PU outsole with tread designed mainly for indoor use. Self-cleaning design and highly non-slip grip.

TECHNOLOGIES

Removable Insole



Highly breathable and absorbent anatomic insole. Multilayer structure to take advantage of the peculiarities of each component. Dry and with a comfortable memory foam "pillow"

Protection elements



Toecap "Alu Sxt 2.0" with differentiated thicknesses, resistant to 200J. Non metal perforation resistant Insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



Lateral stability



Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.

Torsional stability



Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features



ESD footwear discharge static electricity and avoid damaging surrounding objects; they are designed in compliance with the following standards: IEC EN 61340-5-1:2016 - IEC EN 61340-4-3:2018 - IEC EN 61340-4-5:2018.

Other



Double non-slip layer of microfibre, resistant up to 200,000 cycles. Makes the footwear more comfortable, blocking the foot during use.



PU - PU

SOLE 95

SLIP RESISTANCE

EN ISO 20344:2021

BASIC CERAMIC WITH NAILS

FORWARD HEEL SLIP	≥ 0.31	0,32
BACKWARD FOREPART SLIP	≥ 0.36	0,39

SR CERAMIC WITH GLYCERINE

FORWARD HEEL SLIP	≥ 0.19	0,26
BACKWARD FOREPART SLIP	≥ 0.22	0,30